## Rittal – The System.

Faster – better – everywhere.





# SZ 2423.000 Spacer

State: 2025-11-15 (Source: rittal.com/ca-en)



### SZ 2423.000 - Spacer for roof plate

For raising the roof for ventilation purposes, available in three different heights. Not suitable for crane transport.



#### **Features**

Model No.	SZ 2423.000
——————————————————————————————————————	32 2423.000
Product description	For raising the roof for ventilation purposes, available in three
	different heights.
Material	Hexagon steel section
Surface finish	Zinc-plated
Supply includes	Assembly components
Mounting tip	Not suitable for crane transportation
Dimensions	Height: 20 mm
Dimensions	Thread: M12
Suitable for	Enclosure type: VX
	TS
Packaging unit	4 pc(s).
Net weight	0.216
Gross weight	0.255
PCF/VE (cradle-to-gate)	1 kg CO2 eq (Cat B)
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on
class	the basis of the product weight and self-declared
Customs tariff number	73269098

© Rittal 2025

#### **Features**

EAN	4028177022799
E-Number Sweden	E7239675
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3