

Rittal – The System.

Faster – better – everywhere.



SZ 2500.470

Door-Operated Switch

State: 2026-01-29 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2500.470 - Door-Operated Switch for LED System Light

For simple, time-saving connection of the LED system light.

Features

Model No.	SZ 2500.470
Version	With connection cable
Product description	For simple, time-saving connection of the LED system light.
Color	Black
Supply includes	Assembly components
Cross-section	0.75 mm ²
Length	800 mm
AWG	AWG 18
Standards	Mains connection cables: CYJV2 Door-operated switch: NKCR
Dimensions	Width: 31 mm Height: 78 mm Depth: 30 mm Length: 800 mm
Electrical connection	2.5 A
Rated operating voltage	230 V (AC) 24 V (DC)
Packaging unit	1 pc(s).
Net weight	0.1
Gross weight	0.12
Customs tariff number	85365019
EAN	4028177809154
E-Number Sweden	E3465314
ETIM 9	EC002626

Features

ETIM 8 EC002626

ECLASS 8.0 27189266

Approvals

Approvals CQC
CQC-CCC
UL + C-UL (listed)

Explanations Declaration of conformity
Declaration of conformity UK