Rittal – The System.

Faster – better – everywhere.





AX 2503.020 Wall mounting bracket

State: 2025-12-15 (Source: rittal.com/ca-en)



AX 2503.020 - Wall mounting bracket for AX carbon steel, KX carbon steel, AX IT EL

Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.





Features

Model No.	AX 2503.020
Product description	Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.
Benefits	Screw-fastened directly from the rear with a self-tapping screw into the enclosure eyelet
	Simple location of the wall bracket on a pre-configured screw in the wall
	The wall mounting can be optimally adapted to the local conditions via various mounting positions
	As an alternative to a self-tapping screw, the holder can also be
	secured from the inside using a screw and nut
	Additional option for fastening with a nut for dynamic applications
Material	Carbon steel, zinc-plated
Supply includes	Wall mounting bracket
	Cover Caps
	Assembly components
Wall distance	40 mm
Suitable for	Enclosure type: AX carbon steel
	KX carbon steel
	AX IT
	EL
	AX wall-mounted housing, 3-part

© Rittal 2025

Features

Type rating according to UL 50E	Type 1
.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	Type 3R
	Type 4
	Type 12
Packaging unit	4 pc(s).
Net weight	0.56
Gross weight	0.568
PCF/VE (cradle-to-gate)	2.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	83025000
EAN	4028177938274
E-Number Sweden	E3465270
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234

Approvals

Approvals	DNV-GL
	UL + C-UL - FTTA

© Rittal 2025 3