


# Rittal – The System.

Faster – better – everywhere.



## AX 2508.020

### Wall mounting bracket

State: 2026-01-18 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AX 2508.020 - Wall mounting bracket for AX carbon steel, KX carbon steel, AX IT EL

Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.

## Features

Model No.	AX 2508.020
Product description	Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.
Benefits	<p>Screw-fastened directly from the rear with a self-tapping screw into the enclosure eyelet</p> <p>Simple location of the wall bracket on a pre-configured screw in the wall</p> <p>The wall mounting can be optimally adapted to the local conditions via various mounting positions</p> <p>As an alternative to a self-tapping screw, the holder can also be secured from the inside using a screw and nut</p> <p>Additional option for fastening with a nut for dynamic applications</p>
Material	Carbon steel, zinc-plated
Supply includes	Wall mounting bracket Cover Caps Assembly components
Wall distance	20 mm
Suitable for	Enclosure type: AX carbon steel KX carbon steel AX IT EL AX wall-mounted housing, 3-part
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
Packaging unit	4 pc(s).
Net weight	0.44

## Features

---

Gross weight	0.44
PCF/VE (cradle-to-gate)	1.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	83025000
EAN	4028177938281
E-Number Sweden	E3465271
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234

---

## Approvals

---

Approvals	DNV-GL UL + C-UL - FTTA
-----------	----------------------------

---