

Rittal – The System.

Faster – better – everywhere.



SZ 2561.010

Plastic cable gland plates

State: 2026-05-23 (Source: rittal.com, ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

SZ 2561.010 - Plastic cable gland plates with metric knockouts

With pre-punched holes for cable glands.

Features

Model No.	SZ 2561.010
Product description	With pre-punched holes for cable glands. Used with standard flange plate seal.
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	3 x M16 5 x M20 4 x M25 2 x M32 2 x M40
Dimensions	Width: 330 mm Depth: 90 mm
Suitable for	Enclosure type: AE
Gland plate	Size: 3
Operating temperature range	-40 °C...70 °C
Protection category IP to EN 60529	IP 55 if correctly installed
Packaging unit	10 pc(s).
Net weight	1.13 kg
Gross weight	1.396 kg
Customs tariff number	39269097
ETIM 9	EC000211
ETIM 8	EC000211

Features

ECLASS 8.0

27142421

Product description

SZ Plastic cable gland plate, with metric knock-outs, WD: 330x90 mm, size: 3