

Rittal – The System.

Faster – better – everywhere.



SZ 2561.010

Plastic cable gland plates

State: 2025-08-24 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2561.010 - Plastic cable gland plates with metric knockouts

With pre-punched holes for cable glands.

Features

Model No.	SZ 2561.010
Product description	With pre-punched holes for cable glands. Used with standard flange plate seal.
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	3 x M16 5 x M20 4 x M25 2 x M32 2 x M40
Dimensions	Width: 330 mm Depth: 90 mm
Suitable for	Enclosure type: AE
Gland plate	Size: 3
Operating temperature range	-40 °C...70 °C
Protection category IP to EN 60529	IP 55 if correctly installed
Number knockouts	3 5 4 2 2

Features

Metric diameter	M16
	M20
	M25
	M32
	M40
Packaging unit	10 pc(s).
Net weight	1.13
Gross weight	1.396
Customs tariff number	39269097
EAN	4028177550261
E-Number Sweden	E3404762
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421