

Rittal – The System.

Faster – better – everywhere.



SZ 2561.100

Metal gland plate

State: 2025-12-23 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2561.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

Features

Model No.	SZ 2561.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	9 x M20 4 x M25 2 x M32
Dimensions	Width: 330 mm Depth: 90 mm
Suitable for	Enclosure type: AE
Gland plate	Size: 3
Protection category IP to EN 60529	IP66 when mounting in the usual position at the bottom
Number knockouts	9 4 2
Metric diameter	M20 M25 M32
Packaging unit	1 pc(s).
Net weight	0.31
Gross weight	0.356
Customs tariff number	73079100

Features

EAN	4028177390850
E-Number Sweden	E3404795
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421