


# Rittal – The System.

Faster – better – everywhere.



## SZ 2561.300 Plastic Cable Gland Plates

State: 2025-07-16 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2561.300 - Plastic Cable Gland Plates with diaphragms, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

## Features

|  |   |
|--|---|
| Model No.                                      | SZ 2561.300   |
| Product description                            | Just pierce the plastic with a sharp point and pull the cable through.          |
| Material                                       | Plastic to UL 94-V0   |
| Color  | Similar to RAL 7035   |
| Note   | The assignment of the flange plate size can be found on the respective housings |
| Dimensions                                     | Width: 256 mm<br>Depth: 149 mm  |
| Suitable for                                   | Enclosure type: AX  |
| Gland plate                                    | Size: 1   |
| Protection category IP to EN 60529             | IP 66 if correctly installed  |
| Type rating according to UL 50E                | Type 1<br>Type 12   |
| Quantity of cable entries and Ø (mm) min.-max. | 15 x 5-11<br>22 x 10-15<br>8 x 15-25<br>4 x 19-34<br>1 x 26-54                  |
| Packaging unit                                 | 1 pc(s).  |
| Net weight                                     | 0.36  |
| Gross weight                                   | 0.365   |
| Customs tariff number                          | 39269097  |
| EAN  | 4028177935693   |

# Features

|                 |          |
|-----------------|----------|
| E-Number Sweden | E3465288 |
| ETIM 9          | EC000211 |
| ETIM 8          | EC000211 |
| ECLASS 8.0      | 27142421 |

# Approvals

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|