Rittal – The System.

Faster – better – everywhere.





SZ 2561.300 Plastic Cable Gland Plates

State: 2025-10-30 (Source: rittal.com/ca-en)



SZ 2561.300 - Plastic Cable Gland Plates with diaphragms, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

Features

Model No.	SZ 2561.300
Product description	Just pierce the plastic with a sharp point and pull the cable through
Material	Plastic to UL 94-V0
Color	Similar to RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
Dimensions	Width: 256 mm Depth: 149 mm
Suitable for	Enclosure type: AX
Gland plate	Size: 1
Protection category IP to EN 60 529	IP 66 if correctly installed
Type rating according to UL 50E	Type 1
	Type 12
Quantity of cable entries and Ø	15 x 5-11
(mm) minmax.	22 x 10-15
	8 x 15-25
	4 x 19-34
	1 x 26-54
Packaging unit	1 pc(s).
Net weight	0.36
Gross weight	0.365
Customs tariff number	39269097
EAN	4028177935693

© Rittal 2025

Features

E-Number Sweden	E3465288
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3