

Rittal – The System.

Faster – better – everywhere.



SZ 2561.300

Plastic Cable Gland Plates

State: 2026-05-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2561.300 - Plastic Cable Gland Plates with diaphragms, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

Features

| | |
|--|---|
| Model No. | SZ 2561.300 |
| Product description | Just pierce the plastic with a sharp point and pull the cable through. |
| Material | Plastic to UL 94-V0 |
| Color | Similar to RAL 7035 |
| Note | The assignment of the flange plate size can be found on the respective housings |
| Dimensions | Width: 256 mm Depth: 149 mm |
| Suitable for | Enclosure type: AX |
| Gland plate | Size: 1 |
| Protection category IP to EN 60 529 | IP 66 if correctly installed |
| Type rating according to UL 50E | Type 1 Type 12 |
| Quantity of cable entries and Ø (mm) min.-max. | 15 x 5-11 22 x 10-15 8 x 15-25 4 x 19-34 1 x 26-54 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.36 kg |
| Gross weight | 0.365 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000211 |

Features

| | |
|---------------------|--|
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Plastic gland plates, for AX, with membranes, WD: 256x149 mm, for gland plates size 1 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|