

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2561.500**

**Plastic cable gland plates**

State: 2025-08-29 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2561.500 - Plastic cable gland plates with membranes

Pierce the plastic and pull through the cable. With protection category IP 65 when the cable is pulled through carefully.

## Features

Model No.	SZ 2561.500
Product description	Just pierce the plastic with a sharp point and pull the cable through.
Material	Plastic to UL 94-V0 Halogen-free
Color	Similar to RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
Dimensions	Width: 330 mm Depth: 90 mm
Suitable for	Enclosure type: AE
Gland plate	Size: 3
Protection category IP to EN 60529	IP 65
Quantity of cable entries and Ø (mm) min.-max.	17 x 6-11 27 x 10-15 2 x 15-21 4 x 16-25 2 x 19-34
Packaging unit	1 pc(s).
Net weight	0.365
Gross weight	0.37
Customs tariff number	39269097
EAN	4028177325593
E-Number Sweden	E3404727

# Features

ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421