

# Rittal – The System.

Faster – better – everywhere.



SZ 2562.010

Plastic cable gland plates

State: 2026-02-15 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2562.010 - Plastic cable gland plates with metric knockouts

With pre-punched holes for cable glands.

## Features

Model No.	SZ 2562.010
Product description	With pre-punched holes for cable glands. Used with standard flange plate seal.
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	2 x M12 4 x M16 4 x M20 10 x M25 4 x M32 4 x M40 2 x M50
Dimensions	Width: 339 mm Depth: 149 mm
Suitable for	Enclosure type: AE
Gland plate	Size: 4
Operating temperature range	-40 °C...70 °C
Protection category IP to EN 60 529	IP 55 if correctly installed
Number knockouts	2 4 4 10 4 4 2

# Features

Metric diameter	M12 M16 M20 M25 M32 M40 M50
Packaging unit	5 pc(s).
Net weight	0.95
Gross weight	1
Customs tariff number	39269097
EAN	4028177550278
E-Number Sweden	E3404763
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421