

# Rittal – The System.

Faster – better – everywhere.



## SZ 2562.100

### Metal gland plate

State: 2025-07-14 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2562.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

## Features

Model No.	SZ 2562.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	2 x M16 5 x M20 13 x M25 2 x M32 2 x M40
Dimensions	Width: 339 mm Depth: 149 mm
Suitable for	Enclosure type: AE
Gland plate	Size: 4
Protection category IP to EN 60 529	IP66 when mounting in the usual position at the bottom
Number knockouts	2 5 13 2 2
Metric diameter	M16 M20 M25 M32 M40

# Features

Packaging unit	1 pc(s).
Net weight	0.5
Gross weight	0.62
Customs tariff number	73269098
EAN	4028177390867
E-Number Sweden	E3404796
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421