Rittal – The System.

Faster – better – everywhere.





SZ 2562.300 Plastic Cable Gland Plates

State: 2025-12-07 (Source: rittal.com/ca-en)



SZ 2562.300 - Plastic Cable Gland Plates with diaphragms, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

Features

Model No.	SZ 2562.300
Product description	Just pierce the plastic with a sharp point and pull the cable through
Material	Plastic to UL 94-V0
Color	Similar to RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
Dimensions	Width: 339 mm Depth: 149 mm
Suitable for	Enclosure type: AX
Gland plate	Size: 2
Protection category IP to EN 60 529	IP 66 if correctly installed
Type rating according to UL 50E	Type 1
	Type 12
Quantity of cable entries and Ø	24 x 5-11
(mm) minmax.	44 x 10-15
	6 x 15-25
	2 x 19-34
	2 x 26-54
Packaging unit	1 pc(s).
Net weight	0.495
Gross weight	0.5
Customs tariff number	39269097

© Rittal 2025

Features

E-Number Sweden	E3465289
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3