## Rittal – The System.

Faster – better – everywhere.





# SZ 2562.500 Plastic cable gland plates

State: 2025-11-14 (Source: rittal.com/ca-en)



## SZ 2562.500 - Plastic cable gland plates with membranes

Pierce the plastic and pull through the cable. With protection category IP 65 when the cable is pulled through carefully.

#### **Features**

Model No.	SZ 2562.500	
Product description	Just pierce the plastic with a sharp point and pull the cable through	
Material	Plastic to UL 94-V0 Halogen-free	
Color	Similar to RAL 7035	
Note	The assignment of the flange plate size can be found on the respective housings	
Dimensions	Width: 339 mm Depth: 149 mm	
Suitable for	Enclosure type: AE	
Gland plate	Size: 4	
Protection category IP to EN 60 529	IP 65	
Quantity of cable entries and Ø (mm) minmax.	24 x 7-12 48 x 10-15 4 x 15-21 8 x 15-25 4 x 26-35	
Packaging unit	1 pc(s).	
Net weight	0.55	
Gross weight	0.58	
Customs tariff number	39269097	
EAN	4028177325609	
E-Number Sweden	E3404728	

© Rittal 2025

### **Features**

ETIM 9	EC000211	
ETIM 8	EC000211	
ECLASS 8.0	27142421	

© Rittal 2025 3