

**Rittal – The System.**

Faster – better – everywhere.



# SZ 2563.100

## Metal gland plate

State: 2026-02-10 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



# SZ 2563.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

## Features

Model No.	SZ 2563.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	1 x M12 12 x M20 11 x M25 8 x M32 4 x M40
Dimensions	Width: 534 mm Depth: 149 mm
Suitable for	Enclosure type: AE
Gland plate	Size: 5
Protection category IP to EN 60 529	IP66 when mounting in the usual position at the bottom
Number knockouts	1 12 11 8 4
Metric diameter	M12 M20 M25 M32 M40

# Features

Packaging unit	1 pc(s).
Net weight	0.96
Gross weight	1.004
Customs tariff number	73079100
EAN	4028177390874
E-Number Sweden	E3404797
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421