Rittal – The System.

Faster – better – everywhere.



SZ 2563.100 Metal gland plate

State: 2025-11-07 (Source: rittal.com/ca-en)



SZ 2563.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

Features

Model No.	SZ 2563.100
Product description	Simply knock out the holes for the cable glands with a screwdriver
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	1 x M12 12 x M20 11 x M25 8 x M32 4 x M40
Dimensions	Width: 534 mm Depth: 149 mm
Suitable for	Enclosure type: AE
Gland plate	Size: 5
Protection category IP to EN 60 529	IP66 when mounting in the usual position at the bottom
Number knockouts	1 12
	11
	8
	4
Metric diameter	M12
	M20
	M25
	MOO
	M32 M40

© Rittal 2025

Features

Packaging unit	1 pc(s).
Net weight	0.96
Gross weight	1.004
Customs tariff number	73079100
EAN	4028177390874
E-Number Sweden	E3404797
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

© Rittal 2025 3