

Rittal – The System.

Faster – better – everywhere.



SZ 2563.300

Plastic Cable Gland Plates

State: 2026-05-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2563.300 - Plastic Cable Gland Plates with diaphragms, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

Features

Model No.	SZ 2563.300
Product description	Just pierce the plastic with a sharp point and pull the cable through.
Material	Plastic to UL 94-V0
Color	Similar to RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
Dimensions	Width: 447 mm Depth: 149 mm
Suitable for	Enclosure type: AX
Gland plate	Size: 3
Protection category IP to EN 60529	IP 66 if correctly installed
Type rating according to UL 50E	Type 1 Type 12
Quantity of cable entries and Ø (mm) min.-max.	36 x 5-11 46 x 10-15 8 x 15-25 2 x 19-34 4 x 26-35 2 x 26-54
Packaging unit	1 pc(s).
Net weight	0.61 kg
Gross weight	0.63 kg
Customs tariff number	39269097

Features

ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	SZ Plastic gland plates, for AX, with membranes, WD: 447x149 mm, for gland plates size 3

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------