Rittal – The System.

Faster – better – everywhere.





SZ 2564.300 Plastic Cable Gland Plates

State: 2025-11-26 (Source: rittal.com/ca-en)



SZ 2564.300 - Plastic Cable Gland Plates with diaphragms, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

Features

| Model No. | SZ 2564.300 |
|--|---|
| Product description | Just pierce the plastic with a sharp point and pull the cable through |
| Material | Plastic to UL 94-V0 |
| Color | Similar to RAL 7035 |
| Note | The assignment of the flange plate size can be found on the respective housings |
| Dimensions | Width: 534 mm Depth: 149 mm |
| Suitable for | Enclosure type: AX |
| Gland plate | Size: 4 |
| Protection category IP to EN 60 529 | IP 66 if correctly installed |
| Type rating according to UL 50E | Type 1 Type 12 |
| Quantity of cable entries and Ø (mm) minmax. | 28 x 5-11 48 x 10-15 8 x 15-25 2 x 19-34 2 x 26-35 2 x 26-54 1 x 50-110 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.7 |
| Gross weight | 0.736 |
| Customs tariff number | 39269097 |

© Rittal 2025

Features

| EAN | 4028177935723 |
|-----------------|---------------|
| E-Number Sweden | E3465291 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3