Rittal – The System.

Faster – better – everywhere.





AX 2573.100 Metal gland plate

State: 2025-10-29 (Source: rittal.com/ca-en)



AX 2573.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands with a screwdriver.

Features

Model No.	AX 2573.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	4 x M12
	4 x M16
	7 x M20
	15 x M25
	2 x M32
	2 x M40
Dimensions	Width: 447 mm
	Depth: 149 mm
Suitable for	Enclosure type: AX
Gland plate	Size: 3
Protection category IP to EN 60 529	IP 66 if correctly installed
Type rating according to UL 50E	Type 1
	Type 12K
Number knockouts	4
	4
	7
	15
	2
	2

© Rittal 2025

Features

Metric diameter	M12
	M16
	M20
	M25
	M32
	M40
Packaging unit	1 pc(s).
Net weight	0.81
Gross weight	0.82
PCF/VE (cradle-to-gate)	4.1 kg CO2 eq (Cat B)
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on
class	the basis of the product weight and self-declared
Customs tariff number	73079100
EAN	4028177925205
E-Number Sweden	E3465297
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3