

Rittal – The System.

Faster – better – everywhere.



AX 2574.100 Metal gland plate

State: 2026-06-30 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2574.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands with a screwdriver.

Features

| | |
|------------------------------------|---|
| Model No. | AX 2574.100 |
| Product description | Simply knock out the holes for the cable glands with a screwdriver. |
| Material | Carbon steel |
| Color | RAL 7035 |
| Note | The assignment of the flange plate size can be found on the respective housings |
| No. of metric knockouts | 1 x M12 6 x M16 8 x M20 11 x M25 6 x M32 4 x M40 |
| Dimensions | Width: 534 mm Depth: 149 mm |
| Suitable for | Enclosure type: AX |
| Gland plate | Size: 4 |
| Protection category IP to EN 60529 | IP 66 if correctly installed |
| Type rating according to UL 50E | Type 1 Type 12K |
| Packaging unit | 1 pc(s). |
| Net weight | 0.98 kg |
| Gross weight | 0.98 kg |
| PCF/VE (cradle-to-gate) | 4.9 kg CO2 eq (Cat B) |

Features

| | |
|-------------------------------------|--|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73079100 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Metal gland plate, for AX, with metric knockouts, WD: 534x149 mm, for gland plates size 4 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|