

Rittal – The System.

Faster – better – everywhere.



AX 2574.100 Metal gland plate

State: 2025-12-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2574.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands with a screwdriver.

Features

Model No.	AX 2574.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	1 x M12 6 x M16 8 x M20 11 x M25 6 x M32 4 x M40
Dimensions	Width: 534 mm Depth: 149 mm
Suitable for	Enclosure type: AX
Gland plate	Size: 4
Protection category IP to EN 60529	IP 66 if correctly installed
Type rating according to UL 50E	Type 1 Type 12K
Number knockouts	1 6 8 11 6 4

Features

Metric diameter	M12
	M16
	M20
	M25
	M32
	M40
Packaging unit	1 pc(s).
Net weight	0.98
Gross weight	0.98
PCF/VE (cradle-to-gate)	4.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73079100
EAN	4028177925212
E-Number Sweden	E3465298
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------