

Rittal – The System.



Faster – better – everywhere.



AX 2576.100

Metal gland plate

State: 2026-01-30 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

AX 2576.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands with a screwdriver.

Features

Model No.	AX 2576.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	2 x M12 10 x M16 8 x M20 18 x M25 4 x M32 4 x M40
Dimensions	Width: 401 mm Depth: 221 mm
Suitable for	Enclosure type: AX
Gland plate	Size: 6
Protection category IP to EN 60 529	IP 66 if correctly installed
Type rating according to UL 50E	Type 1 Type 12K
Number knockouts	2 10 8 18 4 4

Features

Metric diameter	M12 M16 M20 M25 M32 M40
Packaging unit	1 pc(s).
Net weight	1.07
Gross weight	1.073
PCF/VE (cradle-to-gate)	5.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73079100
EAN	4028177925281
E-Number Sweden	E3465300
ETIM 9	EC000211
ETIM 8	EC000211
ECCLASS 8.0	27142421

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------