

Rittal – The System.

Faster – better – everywhere.



AX 2580.006 Sealing insert

State: 2026-05-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2580.006 - Sealing insert for plastic gland plate, modular and sealing frame, modular

When combined with the inlays, the slotted sealing inserts allow individual cable entry, even for pre-assembled cables.

Features

Model No.	AX 2580.006
Version	Seal insert, small
Product description	When combined with the inlays, the slotted sealing inserts allow individual cable entry, even for pre-assembled cables.
Material	Plastic
Color	RAL 7035
Type rating according to UL 50E	Type 1 Type 12 Type 4X indoor use only
For cable diameter	6 mm
Packaging unit	10 pc(s).
Net weight	0.07 kg
Gross weight	0.073 kg
Customs tariff number	40082900
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Seal inserts, for cable entry, modular, small, for cable diameter 6 mm

Approvals

Approvals

UR + C-UR (recognized)