

Rittal – The System.

Faster – better – everywhere.



TP 2683.600

One-piece consoles

State: 2026-02-02 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TP 2683.600 - One-piece consoles Stainless steel

Console made from stainless steel 1.4301, (AISI 304), ready-to-use unit with high protection category IP 55 in four different widths. Easy handling thanks to self-locking lid stay. Interchangeable lock insert. Easy cable entry thanks to split base plates.



Features

| | |
|--------------------------------------|--|
| Model No. | TP 2683.600 |
| Material | Housing: Stainless steel 1.4301 (AISI 304), 1.5 mm Door or double door and console lid: Stainless steel 1.4301 (AISI 304), 2.0 mm Mounting panel: Carbon steel, 3.0 mm |
| Surface finish | Housing, door, console lid and base plates: Brushed, grain 400 Mounting panel: Zinc-plated |
| Supply includes | Housing, solid back and sides Door or double door at front, with locking rod Console lid with lid stay and cam lock latched in the enclosure Locks with double-bit insert Base plates, divided Mounting panel |
| Dimensions | Width: 600 mm Height: 960 mm |
| Dimensions of mounting plate (W x H) | 530 mm x 780 mm |
| Top depth | 480 mm |

Features

| | |
|--------------------------------------|--|
| Bottom depth | 400 mm |
| Number of doors | 1 |
| Protection category IP to IEC 60 529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Dimensions | Width: 600 mm Height: 960 mm Top depth: 480 mm Bottom depth: 400 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 47.85 |
| Gross weight | 52 |
| Customs tariff number | 94032080 |
| EAN | 4028177031319 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |

Approvals

| | |
|--------------|---|
| Approvals | TÜV UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |