Rittal – The System.

Faster – better – everywhere.





TP 2695.500 TP Universal Consoles

State: 2025-11-16 (Source: rittal.com/ca-en)



TP 2695.500 - TP Universal Consoles

TP universal consoles, high level of stability and IP 55 protection category since the body is mostly manufactured from a single piece. Flexible front design, with option of drawers or desk attached. Easy accessibility due to separate doors. Interchangeable lock insert

Features

Model No.	TP 2695.500
Version	with tall front door
Product modification	The universal console comes with the new mounting plate from the baying enclosure system VX25. Le pupitre universel bénéficie de la nouvelle plaque de montage de l'armoire électrique juxtaposée VX25.
Material	Housing, base plates: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Mounting panel Base Plates
Dimensions	Width: 600 mm Height: 1,300 mm
Dimensions of mounting plate (W x H)	499 mm x 1,196 mm
Top depth	417.5 mm
Bottom depth	500 mm
IK code	IK08
Note	For universal console with short front door: To maintain the protection class, the desk section must be assembled.

© Rittal 2025 2

Features

Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Base material	Carbon steel
Dimensions	Width: 600 mm Height: 1,300 mm Top depth: 417.5 mm Bottom depth: 500 mm
Packaging unit	1 pc(s).
Net weight	74.1
Gross weight	78
Customs tariff number	94032080
EAN	4028177031548
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	TÜV UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3