

# Rittal – The System.

Faster – better – everywhere.



## FT 2735.500 System Window

State: 2025-07-05 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2735.500 - System Window for VX, TS, VX SE

To cover display and operating instruments or cut-outs, and provide protection from dirt and moisture as well as unauthorized access.



## Features

|                     |   |
|---------------------|---|
| Model No.           | FT 2735.500   |
| Version             | 30 section  |
| Product description | Utilized to cover display and operating instruments or cut-outs, and provide protection from dirt and moisture as well as unauthorized access.  |
| Material            | Extruded aluminum section with die-cast zinc corner pieces and single-pane safety glass.  |
| Surface finish      | Base frame: Powder coated on the outside in RAL 7035,<br>Hinge and lock section: Natural-anodized   |
| Value base frame    | Made from single-pane safety glass: high level of resistance to solvents and scratches, anti-static, reduced risk of injury if broken. Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).<br>Hinge with 180° opening angle, easily inserted. |

# Features

|                                     |   |
|-------------------------------------|---|
| Value base frame                    | Easily screw-fastened to the door thanks to modified dimensions (tubular door frame may be used as a drilling template).<br>Readily height-adjustable.<br>Stabilizes the door cut-out.<br>Conceals the cut edge.<br>There is no dirt on the seal, the glass is protected from being lifted out, dirt cannot drop inside, and moisture cannot run behind the window when opening.<br>Frame section height 30 mm or 60 mm |
| Protection category IP to EN 60 529 | IP 54   |
| Note                                | Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).<br>Not suitable for outdoor installation  |
| Suitable for                        | Enclosure type: VX<br>TS<br>VX SE<br>Width: = 600 mm  |
| Dimensions                          | Width: 500 mm<br>Height: 270 mm<br>Depth: 47 mm   |
| Visible area                        | Viewing window width: 363 mm<br>Viewing window height: 198 mm   |
| Build depth for components (max.)   | 33 mm   |
| Packaging unit                      | 1 pc(s).  |
| Net weight                          | 3.016   |
| Gross weight                        | 3.22  |
| Customs tariff number               | 76101000  |
| EAN                                 | 4028177476288   |
| ETIM 9                              | EC002527  |
| ETIM 8                              | EC002527  |
| ECLASS 8.0                          | 27182301  |

# Approvals

---

Certificates

Protection category