

Rittal – The System.

Faster – better – everywhere.



FT 2760.010

Viewing Windows

State: 2026-01-11 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FT 2760.010 - Viewing Windows for AX

For external mounting on AX enclosures instead of a door and on surfaces.



Features

Model No.	FT 2760.010
Version	60 section
Product description	For mounting on AX housing instead of door and on surfaces.
Material	Frame: Aluminum, natural anodized. Glass panel: Acrylic
Supply includes	Plastic handle with lock insert # 3524 E
Protection category IP to EN 60 529	IP 54
Suitable for Model No.	1039.000 1339.000 1009.000
Suitable for	Enclosure type: AX Width: = 600 mm Height: = 380 mm
Dimensions	Width: 597 mm Height: 377 mm Depth: 62 mm
Visible area	Viewing window width: 537 mm Viewing window height: 317 mm

Features

Build depth for components (max.) 58 mm

Packaging unit 1 pc(s).

Net weight 3.245

Gross weight 3.3

Customs tariff number 76101000

EAN 4028177938571

ETIM 9 EC002527

ETIM 8 EC002527

ECLASS 8.0 27182204