## Rittal – The System.

Faster – better – everywhere.





# FT 2760.010 Viewing Windows

State: 2025-11-18 (Source: rittal.com/ca-en)



## FT 2760.010 - Viewing Windows for AX

For external mounting on AX enclosures instead of a door and on surfaces.







#### **Features**

Model No.	FT 2760 010
	FT 2760.010
Version	60 section
Product description	For mounting on AX housing instead of door and on surfaces.
Material	Frame: Aluminum, natural anodized.
	Glass panel: Acrylic
Supply includes	Plastic handle with lock insert # 3524 E
Protection category IP to EN 60	IP 54
529	
Suitable for Model No.	1039.000
	1339.000
	1009.000
Suitable for	Enclosure type: AX
	Width: = 600 mm
	Height: = 380 mm
Dimensions	Width: 597 mm
	Height: 377 mm
	Depth: 62 mm
Visible area	Viewing window width: 537 mm

© Rittal 2025

### **Features**

Build depth for components (max.)	58 mm
Packaging unit	1 pc(s).
Net weight	3.245
Gross weight	3.3
Customs tariff number	76101000
EAN	4028177938571
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204

© Rittal 2025 3