

Rittal – The System.

Faster – better – everywhere.



FT 2780.000 Acrylic glazed cover

State: 2025-08-25 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2780.000 - Acrylic glazed cover

To protect display and control components in standard 19" or metric dimensions.

Features

| | |
|------------------------------------|--|
| Model No. | FT 2780.000 |
| Version | 19" |
| Product description | With security lock, lock no. 3524 E. |
| Material | Frame: Extruded aluminum sections with die-cast corner pieces Glass panel: Smoked acrylic |
| Supply includes | Hinges and assembly components. Incl. lock insert # 3524 E |
| Protection category IP to EN 60529 | IP 54 |
| Dimensions | Width: 320 mm Height: 158 mm Depth: 47.5 mm |
| Visible area | Viewing window width: 280 mm Viewing window height: 137.5 mm |
| Build depth for components (max.) | 43 mm |
| Installation dimensions | Installation depth for components: 269.2 mm Installation width for components: ½ 19" |
| Packaging unit | 1 pc(s). |
| Net weight | 0.937 |
| Gross weight | 1.137 |
| Customs tariff number | 39269097 |
| EAN | 4028177032217 |
| ETIM 9 | EC002527 |
| ETIM 8 | EC002527 |
| ECLASS 8.0 | 27182301 |