


Rittal – The System.

Faster – better – everywhere.



FT 2784.000 Acrylic glazed cover

State: 2025-08-16 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2784.000 - Acrylic glazed cover

To protect display and control components in standard 19" or metric dimensions.

Features

Model No.	FT 2784.000
Version	metric
Product description	With security lock, lock no. 3524 E.
Material	Frame: Extruded aluminum sections with die-cast corner pieces Glass panel: Smoked acrylic
Supply includes	Hinges and assembly components. Incl. lock insert # 3524 E
Protection category IP to EN 60529	IP 54
Dimensions	Width: 400 mm Height: 200 mm Depth: 47.5 mm
Visible area	Viewing window width: 360 mm Viewing window height: 179.5 mm
Build depth for components (max.)	43 mm
Packaging unit	1 pc(s).
Net weight	1.3
Gross weight	1.4
Customs tariff number	39269097
EAN	4028177032279
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182301