

# Rittal – The System.

Faster – better – everywhere.



## FT 2789.000

## Acrylic glazed cover

State: 2025-07-18 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2789.000 - Acrylic glazed cover

To protect display and control components in standard 19" or metric dimensions.

## Features

Model No.	FT 2789.000
Version	metric
Product description	With security lock, lock no. 3524 E.
Material	Frame: Extruded aluminum sections with die-cast corner pieces Glass panel: Smoked acrylic
Supply includes	Hinges and assembly components. Incl. lock insert # 3524 E
Protection category IP to EN 60529	IP 54
Dimensions	Width: 600 mm Height: 400 mm Depth: 47.5 mm
Visible area	Viewing window width: 560 mm Viewing window height: 379.5 mm
Build depth for components (max.)	43 mm
Packaging unit	1 pc(s).
Net weight	2.46
Gross weight	2.68
Customs tariff number	39269097
EAN	4028177032378
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182301