

# Rittal – The System.

Faster – better – everywhere.



FT2793.560

## Viewing Windows

Since: 2026-01-28 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2793.560 - Viewing Windows Stainless steel

To cover display and operating instruments or cut-outs, and provide protection from dirt and moisture as well as unauthorized access. Material stainless steel 1.4301 (AISI 304).



## Features

Model No.	FT 2793.560
Product description	Equipped as standard with internal 130° hinges and all-round seal.
Material	Stainless steel 1.4301 (AISI 304) Single-pane safety glass
Supply includes	Assembly components
Protection category IP to EN 60 529	IP 54
Note	Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).
Dimensions	Width: 522 mm Height: 600 mm Depth: 38 mm
Visible area	Viewing window width: 408 mm Viewing window height: 543 mm

# Features

---

Build depth for components (max.) 31 mm

---

Packaging unit 1 pc(s).

---

Net weight 6.175

---

Gross weight 6.5

---

Customs tariff number 76101000

---

EAN 4028177149656

---

ETIM 9 EC002527

---

ETIM 8 EC002527

---

ECLASS 8.0 27182204