

Rittal – The System.

Faster – better – everywhere.



AX 2820.102

Base/plinth corner pieces with base/plinth trim panels, front and rear, 200 mm

State: 2025-05-08 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2820.102 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 200 mm for AX

Base/plinth corner piece with a large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.

Features

Model No.	AX 2820.102
Product description	Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.
Material	Base/plinth corner piece: Carbon steel Base/plinth trim panels, front/rear: Carbon steel Corner cover: Plastic
Color	RAL 9005
Supply includes	4 x base/plinth corner pieces, 200 mm high 4 x corner covers 1 base/plinth trim panel, front/rear, 200 mm 2 x base/plinth trim panels, front/rear, 100 mm high Assembly components
Note	Base/plinth covers for side completion of a base/plinth unit Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system
Dimensions	Height: 200 mm
Suitable for	Enclosure type: AX Width: = 1,000 mm
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
Packaging unit	2 pc(s).
Net weight	9.8

Features

Gross weight	10.8
Customs tariff number	94039910
EAN	4028177942592
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------