

# Rittal – The System.

Faster – better – everywhere.



## SZ 2899.200 Stepped Collar

State: 2026-05-14 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2899.200 - Stepped Collar For wall thicknesses from 1.5 to 4.5 mm

To insert cable simply cut off at the required level to match the cable diameter.



## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SZ 2899.200  |
| Product description                 | To insert cable, simply cut off at the required level to match the cable diameter. |
| Applications                        | For wall thicknesses from 1.5 to 4.5 mm  |
| Material                            | Cover: Thermoplastic elastomer   |
| Dimensions                          | Thread: M20  |
| For wall thickness (max.)           | 1.5 - 4.5 mm   |
| Protection category IP to IEC 60529 | IP 54 with careful cable entry   |
| For cable diameters                 | 5 - 16 mm  |
| Packaging unit                      | 100 pc(s).   |
| Net weight                          | 0.2 kg   |
| Gross weight                        | 0.252 kg   |
| Customs tariff number               | 39269097   |
| ETIM 9                              | EC000879   |
| ETIM 8                              | EC000879   |
| ECLASS 8.0                          | 27069216   |

# Features

---

Product description

SZ Stepped collar, for wall thickness from 1,5 bis 4,5 mm, for hole M20, Sealing range: 5-16 mm