Rittal – The System.

Faster – better – everywhere.





SZ 2899.320 Stepped Collar

State: 2025-11-18 (Source: rittal.com/ca-en)



SZ 2899.320 - Stepped Collar For wall thicknesses from 1.5 to 4.5 mm

To insert cable simply cut off at the required level to match the cable diameter.



Features

Model No.	SZ 2899.320
Product description	To insert cable, simply cut off at the required level to match the cable diameter.
Applications	For wall thicknesses from 1.5 to 4.5 mm
Material	Cover: Thermoplastic elastomer
Dimensions	Thread: M32
For wall thickness (max.)	1.5 - 4.5 mm
Protection category IP to IEC 60 529	IP 54 with careful cable entry
For cable diameters	13 - 26.5 mm
Packaging unit	25 pc(s).
Net weight	0.1
Gross weight	0.144
Customs tariff number	39269097
EAN	4028177389625
ETIM 9	EC000879
ETIM 8	EC000879

© Rittal 2025

Features

ECLASS 8.0

27069216

© Rittal 2025 3