### Rittal – The System.

Faster – better – everywhere.





# SV 3052.000 Busbar Supports

State: 2025-11-04 (Source: rittal.com/ca-en)



### SV 3052.000 - Busbar Supports

For 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm) busbar systems.

#### **Features**

| Model No.             | SV 3052.000  |
|-----------------------|--|
| Material              | Fiberglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0 |
| Color                 | RAL 7035   |
| Number of poles       | 3-pole<br>185 mm   |
| Suitable for busbars  | 50 x 10<br>60 x 10<br>80 x 10  |
| Rated current max.    | 1,600 A  |
| Note on Model No.:    | The base component of the busbar support may also be used as a single-pole support.            |
| Dimensions            | Width: 24 mm<br>Height: 515 mm<br>Depth: 51 mm   |
| Packaging unit        | 2 pc(s).   |
| Net weight            | 1.26   |
| Gross weight          | 1.338  |
| Customs tariff number | 85369010   |
| EAN                   | 4028177035751  |
| ETIM 9                | EC001166   |
| ETIM 8                | EC001166   |
| ECLASS 8.0            | 27400607   |

© Rittal 2025

## Approvals

| Approvals    | ABS                          |
|--------------|------------------------------|
| Explanations | Declaration of conformity    |
|              | Declaration of conformity UK |

© Rittal 2025 3