

# Rittal – The System.

Faster – better – everywhere.



## SV 3052.000 Busbar Supports

State: 2026-07-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3052.000 - Busbar Supports

For 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm) busbar systems.



## Features

|                       |   |
|-----------------------|---|
| Model No.             | SV 3052.000   |
| Material              | Fiberglass-reinforced, thermoplastic polyester (PBT)<br>Fire protection corresponding to UL 94-V0 |
| Color                 | RAL 7035  |
| Number of poles       | 3-pole<br>185 mm  |
| Suitable for busbars  | 50 x 10<br>60 x 10<br>80 x 10   |
| Rated current max.    | 1,600 A   |
| Note on Model No.:    | The base component of the busbar support may also be used as a single-pole support.               |
| Dimensions            | Width: 24 mm<br>Height: 515 mm<br>Depth: 51 mm  |
| Packaging unit        | 2 pc(s).  |
| Net weight            | 1.26 kg   |
| Gross weight          | 1.338 kg  |
| Customs tariff number | 85369010  |
| ETIM 9                | EC001166  |

# Features

---

|                     |  |
|---------------------|--|
| ETIM 8              | EC001166   |
| ECLASS 8.0          | 27400607   |
| Product description | SV Busbar support, 3-pole, 185 mm bar centre distance, for busbar<br>WH: 50-80x10 mm |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | ABS   |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |