

Rittal – The System.

Faster – better – everywhere.



SV 3073.000 Busbar Supports

State: 2026-05-14 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3073.000 - Busbar Supports

For 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm) busbar systems.



Features

Model No.	SV 3073.000
Material	Fiberglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Color	RAL 7035
Number of poles	3-pole 100 mm
Suitable for busbars	30 x 10 40 x 10 50 x 10 60 x 10
Rated current max.	1,250 A
Dimensions	Width: 22 mm Height: 320 mm Depth: 70 mm
Packaging unit	4 pc(s).
Net weight	1.612 kg
Gross weight	1.83 kg
Customs tariff number	85469010
ETIM 9	EC001166
ETIM 8	EC001166

Features

ECLASS 8.0	27400607
Product description	SV Busbar support, 3-pole, 100 mm bar centre distance, for busbar WH: 30-60x10 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---