Rittal – The System.

Faster - better - everywhere.





SK 3108.115 Enclosure internal fan

State: 2025-11-07 (Source: rittal.com/ca-en)




SK 3108.115 - Enclosure internal fan

To prevent hot spots inside the enclosure and facilitate the ventilation of active enclosure climate control components.







Features

Model No.	SK 3108.115	
Product description	To prevent hot-spots and support the air routing of active enclose climate control components. Adjustable in two axes. Mounted or the frame section. Several fans can be cascaded using the quick-release terminal strip.	
Supply includes	Complete unit ready for connection with axial fan Snap-on pivot device Fasteners	
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz	
Rated power Pel	At 50 Hz: 19 W At 60 Hz: 18 W	
Rated current max.	At 50 Hz: 0.24 A At 60 Hz: 0.23 A	
Packaging unit	1 pc(s).	
Net weight	0.96	
Gross weight	1.136	
Customs tariff number	84145915	
EAN	4028177220492	

© Rittal 2025

Features

ETIM 9	EC000320	
ETIM 8	EC000320	
ECLASS 8.0	27180716	

Approvals

Explanations Declaration of conformity

© Rittal 2025 3