

# Rittal – The System.

Faster – better – everywhere.



## SK 3130.100

## TopTherm air-air heat exchanger

State: 2025-08-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3130.100 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SK 3130.100  |
| Version                             | wall-mounted   |
| Product description                 | Air-to-air heat exchangers are especially suitable for aggressive environments since the internal and external circuit are completely separated from each other by two air circuits. |
| Color                               | RAL 7035   |
| Supply includes                     | Complete unit ready for connection<br>Plug-in terminal strip<br>Floating fault signal contact in case of overtemperature<br>Drilling template<br>Fasteners                           |
| Specific thermal output             | 90 W/K   |
| Air throughput (unimpeded air flow) | External circuit at 50 Hz: 850 m³/h<br>External circuit at 60 Hz: 945 m³/h<br>Internal circuit at 50 Hz: 850 m³/h<br>Internal circuit at 60 Hz: 945 m³/h                             |
| Rated operating voltage             | 230 V, 1~, 50 Hz/60 Hz   |
| Rated current max.                  | At 50 Hz: 1.35 A<br>At 60 Hz: 1.8 A  |
| Dimensions                          | Width: 400 mm<br>Height: 1,580 mm<br>Depth: 215 mm   |
| Pre-fuse                            | Miniature circuit-breaker/fuse: 4 A  |
| Temperature control                 | Electronic Control with Digital Display (factory setting +35 °C)   |
| Operating temperature range         | -5 °C...55 °C  |

# Features

|                                     |  |
|-------------------------------------|--|
| Protection category IP to IEC 60529 | Internal circuit, IP 54<br>External circuit, IP 34 |
| Packaging unit                      | 1 pc(s).   |
| Net weight                          | 37.05  |
| Gross weight                        | 39   |
| Customs tariff number               | 84158300   |
| EAN                                 | 4028177388994                                      |
| ETIM 9                              | EC002514   |
| ETIM 8                              | EC002514   |
| ECLASS 8.0                          | 27180711   |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |