

# Rittal – The System.

Faster – better – everywhere.



## SK 3164.115 Roof-Mounted Fans

State: 2026-03-13 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3164.115 - Roof-Mounted Fans for VX, VX IT

Roof-mounted fan for the office sector with minimal noise level (40 dB) and high volumetric flow (unimpeded air flow 1500 m<sup>3</sup>/h).



## Features

Model No.	SK 3164.115
Benefits	Easy assembly, the roof plate variant eliminates the need to create mounting cut-outs Wired ready for connection
Material	Carbon steel, spray finished
Color	RAL 7035
Supply includes	Roof-Mounted Fans Assembly components
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz 110 V (DC)
Rated current max.	At 50 Hz: 0.6 A At 60 Hz: 0.7 A
Dimensions	Width: 511 mm Height: 227 mm Depth: 511 mm
Protection category IP to IEC 60529	Internal circuit, IP 54
Note	Reduction of the specified air flow to 800 m <sup>3</sup> /h at 40 Pa counter-pressure using two ventilated base/plinth trim panels
Operating temperature range	20 °C...55 °C

# Features

---

Packaging unit	1 pc(s).
Net weight	18.445 kg
Gross weight	19.416 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

# Approvals

---

Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK