Rittal - The System.

Faster – better – everywhere.





SK 3171.105 Chopped fiber filter mat

State: 2025-12-14 (Source: rittal.com/ca-en)



SK 3171.105 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

Features

| Model No. | SK 3171.105 |
|------------------------|---|
| Version | for filter fans |
| Product description | Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material | Chemical fibers |
| Note | Not suitable for use in EMC filter fans. |
| Suitable for Model No. | 3239 |
| Dimensions | Width: 173 mm Height: 173 mm Depth: 17 mm |
| Filter class | to DIN EN 779: G3 to DIN EN ISO 16890: ISO coarse 50% |
| Packaging unit | 50 pc(s). |
| Net weight | 0.65 |
| Gross weight | 0.76 |
| Customs tariff number | 56039390 |
| EAN | 4028177695559 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |
| | |

© Rittal 2025 2

Approvals

| Approvals | UR + C-UR (recognized) |
|--------------|------------------------|
| Certificates | EAC |

© Rittal 2025 3