

Rittal – The System.

Faster – better – everywhere.



SK 3172.100 Chopped fiber filter mat

State: 2026-05-05 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3172.100 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

Features

| | |
|------------------------|---|
| Model No. | SK 3172.100 |
| Version | for filter fans |
| Product description | Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material | Chemical fibers |
| Note | Not suitable for use in EMC filter fans. |
| Suitable for Model No. | 3240.... 3241.... |
| Dimensions | Width: 221 mm Height: 221 mm Depth: 17 mm |
| Filter class | to DIN EN 779: G3 to DIN EN ISO 16890: ISO coarse 50% |
| Packaging unit | 5 pc(s). |
| Net weight | 0.095 kg |
| Gross weight | 0.1 kg |
| Customs tariff number | 56039390 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |
| Product description | SK spare filter mats, for filter fans, for SK 3240.../3241..., WHD: 221 x 221 x 17 mm |

Approvals

Approvals

UR + C-UR (recognized)