

Rittal – The System.

Faster – better – everywhere.



SK 3172.120

Pleated filter

State: 2026-02-08 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

SK 3172.120 - Pleated filter for filter and roof-mounted fans, cooling units and chillers

Compared to conventional chopped fiber filters, the high-quality pleated filter technology enables a significant increase in the volume flow and thus an increase in the performance of the unit as well as a reduction in energy consumption. In addition, better filtration properties ensure less dust in the enclosure or unit, and the longer service life means significantly lower service costs.



Features

Model No.	SK 3172.120
Version	for fan-and-filter units / outlet filters
Material	PET
Color	White
Note	Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
Suitable for Model No.	3240.xxx 3241.xxx
Dimensions	Width: 212.5 mm Height: 212.5 mm Depth: 21 mm
Filter class	to DIN EN 779: G4 to DIN EN ISO 16890: ISO coarse 70%
Protection category IP to IEC 60 529	IP 54 when mounted in filter & roof-mounted fans/outlet filters
Note on Model No.:	Not suitable for use in EMC filter fans.

Features

Packaging unit 5 pc(s).

Net weight 0.335

Gross weight 0.34

Customs tariff number 56039390

EAN 4028177969148

ETIM 9 EC002513

ETIM 8 EC002513

ECLASS 8.0 27180706

Approvals

Approvals UR + C-UR (recognized)