

Rittal – The System.

Faster – better – everywhere.



SK 3237.066

Chopped fiber filter mat

State: 2026-07-10 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3237.066 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

Features

| | |
|------------------------|---|
| Model No. | SK 3237.066 |
| Version | for EMC filter fans |
| Product description | Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material | Copper/nickel/chrome-coated chemical fibers |
| Note | Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats. |
| Suitable for Model No. | 3237.060/3237.6xx |
| Dimensions | Width: 92 mm Height: 92 mm Depth: 10 mm |
| Filter class | to DIN EN 779: G2 |
| Packaging unit | 5 pc(s). |
| Net weight | 0.005 kg |
| Gross weight | 0.009 kg |
| Customs tariff number | 56039390 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |
| Product description | SK spare filter mats, for EMC-filter fans, for SK 3237.6.., WHD: 92 x 92 x 10 mm |