# Rittal – The System.

Faster – better – everywhere.





# SK 3237.208 **Outlet Filters**

State: 2025-11-21 (Source: rittal.com/ca-en)



### SK 3237.208 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



#### **Features**

Model No.	SK 3237.208
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Color	RAL 9005
Supply includes	Outlet Filters Chopped fiber filter mat
Mounting cut-out	Width of opening: 92 mm Cut-out height: 92 mm
Suitable for Model No.	SK 3237.1xx
Dimensions	Width: 116.5 mm Height: 116.5 mm Depth: 16 mm
Protection category NEMA	Type 12 with fleece filter Type 3 Type 3R with fleece filter and hose-proof hood
Protection category IP to IEC 60 529	IP 54 with fleece filter IP 56 with fleece filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.13

© Rittal 2025

## Features

Gross weight	0.14
Customs tariff number	39269097
EAN	4028177663435
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

# **Approvals**

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3