## Rittal – The System.

Faster - better - everywhere.





# SK 3238.080 Hose-proof hood

State: 2025-11-18 (Source: rittal.com/ca-en)



### SK 3238.080 - Hose-proof hood Stainless steel

The Rittal stainless steel fan shroud is engineered for rugged indoor and outdoor use. Its durable finish carries UL Type 3R and 4X certifications (model 3237 Type 12, 3R only) to guard against large debris, heavy rain, hose-directed water sprays, and corrosion. A blue silicone gasket—rooted in Rittal's Food & Beverage expertise—ensures superior hygiene and simplifies washdown cleaning.







2

#### **Features**

Model No.	SK 3238.080
Product description	For fan-and-filter units/outlet filters. Easy cleaning thanks to external, food-safe silicone seal.
Material	Stainless steel AISI304 - 1.4301 (V2A) Silicone
Suitable for Model No.	3238
Dimensions	Width: 176 mm Height: 245 mm Depth: 55 mm
Protection category NEMA	NEMA 1 NEMA 12 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
Protection category IP to IEC 60 529	IP 56 when fitted over fan-and-filter unit/outlet filter with filter mat
Packaging unit	1 pc(s).

© Rittal 2025

## Features

Net weight	1.4
Gross weight	1.54
Customs tariff number	94039910
EAN	4028177651685
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405

## **Approvals**

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)	
Certificates	EAC	

© Rittal 2025 3