# Rittal - The System.

Faster – better – everywhere.





# SK 3240.080 Hose-proof hood

State: 2025-12-14 (Source: rittal.com/ca-en)



## SK 3240.080 - Hose-proof hood Stainless steel

The Rittal stainless steel fan shroud is engineered for rugged indoor and outdoor use. Its durable finish carries UL Type 3R and 4X certifications (model 3237 Type 12, 3R only) to guard against large debris, heavy rain, hose-directed water sprays, and corrosion. A blue silicone gasket—rooted in Rittal's Food & Beverage expertise—ensures superior hygiene and simplifies washdown cleaning.







2

#### **Features**

Model No.	SK 3240.080
Product description	For fan-and-filter units/outlet filters. Easy cleaning thanks to external, food-safe silicone seal.
Material	Stainless steel AISI304 - 1.4301 (V2A)
	Silicone
Suitable for Model No.	3240
	3241
Dimensions	Width: 282 mm
	Height: 390 mm
	Depth: 85 mm
Protection category NEMA	NEMA 1
	NEMA 12
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 4X
Protection category IP to IEC 60 529	IP 56 when fitted over fan-and-filter unit/outlet filter with filter

© Rittal 2025

## **Features**

Packaging unit	1 pc(s).
Net weight	3.123
Gross weight	3.323
Customs tariff number	94039910
EAN	4028177651920
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405

## **Approvals**

Approvals	CSA
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Certificates	EAC

© Rittal 2025 3