

Rittal – The System.

Faster – better – everywhere.



SK 3240.200

Outlet Filters

State: 2026-01-18 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

SK 3240.200 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



Features

Model No.	SK 3240.200
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Color	RAL 7035
Supply includes	Outlet Filters Chopped fiber filter mat
Mounting cut-out	Width of opening: 224 mm Cut-out height: 224 mm
Suitable for Model No.	3240.1xx/3240.5xx/3241.1xx/3241.5xx
Dimensions	Width: 255 mm Height: 255 mm Depth: 25 mm
Protection category NEMA	Type 12 with chopped fiber filter/pleated filter Type 3 Type 3R Type 4 Type 4X with chopped fiber filter/pleated filter and hose-proof hood
Protection category IP to IEC 60 529	IP 54 with chopped fiber filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped fiber filter/pleated filter and hose-proof hood

Features

Packaging unit 1 pc(s).

Net weight 0.56

Gross weight 0.582

Customs tariff number 39269097

EAN 4028177651975

E-Number Sweden E3404361

ETIM 9 EC002513

ETIM 8 EC002513

ECLASS 8.0 27180706

Approvals

Approvals CSA
UL + C-UL - FTTA
UR + C-UR (recognized)

Certificates EAC

Explanations Declaration of conformity